

501

BALDOR • RELIANCE Stock Product Catalog

The Industry's Most Preferred



BALDOR®



501 Section Headings

General Information	5	IEC Frame Motors	175
Premium Efficient Super-E® Motors	8	50 Hertz Motors	185
Single Phase Motors	32	Inverter Drive® / Vector Drive® Motors & Controls	189
General Purpose Industrial Motors	38	DC Motors and Controls	267
Severe Duty Motors	58	Soft Starters and Dynamic Brakes	325
Washdown Duty Motors.....	77	Gearmotors and Gear Products	333
Explosion Proof Motors.....	87	Motor Accessories	386
Pump Motors	97	Grinders	398
Commercial Motors	112	Generators	407
HVAC Motors.....	120	Servo Motors and Controls	413
Farm Duty Motors.....	133	Mod Express	414
Definite Purpose Motors.....	140	Baldor Education Workshops	448
Unit Handling Motors	151	Warranties and Sales Policies	453
Brake Motors	155	Cross Reference and Index	455
200 and 575 Volt Motors.....	160	Baldor Sales Offices	543



Baldor•Reliance® large motors are trusted to get the job done! Designed and built for superior reliability, energy savings and rugged performance...Baldor•Reliance is the preferred choice. With ratings to 1,500 Hp delivered from stock and the shortest lead-times available for custom motors to 15,000 Hp, no application is too tough for Baldor•Reliance motors.

Invest in Gold



BALDOR • RELIANCE

Electric motors consume 63 percent of all electricity used in U.S. industry. Designed and built to meet or exceed NEMA Premium® efficiency standards, Baldor•Reliance® Super-E® motors run cooler, last longer and cost less every minute they operate.

Fractional to 15,000 Hp, Baldor•Reliance Super-E motors reduce your electricity costs with a return on your investment that's as good as gold.

baldor.com

- Energy Efficient
- Unmatched Quality
- Superior Reliability
- Quickest Delivery Available

BALDOR