



BALDOR GENERATORS

GENERAL INSTALLATION FOR IDLC GENERATORS


UL2200 MODEL #	MODEL #	OVERALL LENGTH L	OVERALL WIDTH W	OVERALL HEIGHT H	HOOD LENGTH HL	BASE HEIGHT BW	MOUNTING HOLE 1 M1	MOUNTING HOLE 2 M2	MOUNTING WIDTH MW	TANK HEIGHT TH (12-17 HRS)	TANK HEIGHT TH (24-34 HRS)	TANK HEIGHT TH (FRAME ONLY)
IDLC180-3JU	IDLC180-3J	180	63	94	42	54	28.00	98.00	51.00	11	20	6
IDLC200-3JU	IDLC200-3J			106			20.00	96.00		14	25	
IDLC225-3JU	IDLC225-3J			108								
IDLC250-3JU	IDLC250-3J											
IDLC275-3JU	IDLC275-3J											




PLAN VIEW




REAR VIEW




PLAN VIEW OF TANK ONLY



RIGHT SIDE VIEW



FRONT VIEW



LEFT SIDE VIEW

NOTES:

FOR PRODUCT DATA REFER TO
BALDOR MODEL SPEC SHEETS

FOR INSTALLATION RECOMMENDATIONS
REFER TO GEN SET MANUAL MN2407

ALL DIMENSIONS IN INCHES

DRAWING TO SCALE

TOLERANCES UNLESS OTHERWISE SPECIFIED
DECIMALS .XX ±.25 FRACTIONS ±1/4

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: UPDATE TABLE		
REV. LTR: C	VERSION: 03	TDR: 000000451565
FILE: \PGA\00010\468	REVISED: 14: 27 12/13/2007	BY: PGCONB0
MTL: -	TAB: SA_L1_180_275	

BALDOR • DODGE • RELIANCE

IDLC 30-500-07E