



BALDOR GENERATORS

GENERAL INSTALLATION FOR IDLC GENERATORS


UL2200 MODEL #	MODEL #	OVERALL LENGTH L	OVERALL WIDTH W	OVERALL HEIGHT H	HOOD LENGTH HL	BASE WIDTH BW	MOUNTING HOLE 1 M1	MOUNTING HOLE 2 M2	MOUNTING WIDTH MW	TANK HEIGHT TH (12-17 HRS)	TANK HEIGHT TH (24-34 HRS)	TANK HEIGHT TH (FRAME ONLY)
IDLC180-3J	IDLC180-3J	222	102	96	42	54	28.00	98.00	51.00	11	20	8
IDLC200-3J	IDLC200-3J			108								
IDLC225-3J	IDLC225-3J			110								
IDLC250-3J	IDLC250-3J						20.00	96.00		14	25	
IDLC275-3J	IDLC275-3J											




PLAN VIEW




REAR VIEW




PLAN VIEW OF TANK ONLY



RIGHT SIDE VIEW



FRONT VIEW



LEFT SIDE VIEW

NOTES:

FOR PRODUCT DATA REFER TO BALDOR MODEL SPEC SHEETS

FOR INSTALLATION RECOMMENDATIONS REFER TO GEN SET MANUAL MN2407

ALL DIMENSIONS IN INCHES

DRAWING TO SCALE

TOLERANCES UNLESS OTHERWISE SPECIFIED
DECIMALS .XX ±.25 FRACTIONS ±1/4

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: UPDATE TABLE		
REV. LTR: C	VERSION: 03	TDR: 000000451565
FILE: \PGA\00010\468	REVISED: 14:27:42 12/13/2007	BY: PGCONBO
MTL: -	TAB: SA_L2_180_275	

BALDOR • DODGE • RELIANCE

IDLC 30-500-07E